



A	Skin	Size		
	38.5" x 38.5"	W	Diamond Shown as it will appear on the Xpressions unit	Diamond
		H		
B	Skin	Size		
	38.5" x 38.5"	W	Diamond Shown as it will appear on the Xpressions unit	Diamond
		H		
C	Skin	Size		
	28.5" x 28.5"	W	1x1 Single Twist Shown as it will appear on the Xpressions unit	1x1 Single Twist
		H		
D	Skin	Size		
	28" x 30"	W	1x1 Vertical Thread Shown as it will appear on the Xpressions unit	1x1 Vertical Thread
		H		
E	Skin	Size		
	28" x 30"	W	1x1 Vertical Thread Shown as it will appear on the Xpressions unit	1x1 Vertical Thread
		H		
F	Skin	Size		
	28.5" x 28.5"	W	1x1 Single Twist Shown as it will appear on the Xpressions unit	1x1 Single Twist
		H		
G	Skin	Size		
	28.5" x 28.5"	W	1x1 Single Twist Shown as it will appear on the Xpressions unit	1x1 Single Twist
		H		
H	Skin	Size		
	28" x 28"	W	1x1 Flat Back Shown as it will appear on the Xpressions unit	1x1 Flat Back
		H		
I	Skin	Size		
	38.5" x 38.5"	W	Diamond Shown as it will appear on the Xpressions unit	Diamond
		H		
J	Skin	Size		
	38.5" x 38.5"	W	Diamond Shown as it will appear on the Xpressions unit	Diamond
		H		
K	Skin	Size		
	28" x 28"	W	1x1 Flat Back Shown as it will appear on the Xpressions unit	1x1 Flat Back
		H		
L	Skin	Size		
	28.5" x 28.5"	W	1x1 Single Twist Shown as it will appear on the Xpressions unit	1x1 Single Twist
		H		

It is recommended that all text and borders be 2" from the finish size

Focus Area Key
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes
 see xpressions-snap.com for details