



## XPR SM 3Q C



	Α	Skin	Size	
	, Z <sup>E</sup>	, S. J. S. J	14.25"	w
	7k. / 3.		Х	<u> </u>
			14.25"	Н
	1v1 Si	ngle Twist	1x1 Single Twist Shown as it will appear on the Xpressions unit	
	TAT SITISTE TWIST Apressions unit			
	В	Skin	Size	
	۲,	5/1/2	14.25"	W
	14.		х	_
	~	\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \	14.25"	Н
	<u> </u>		1x1 Single Twist Shown as it will appear on the	
	1x1 Si	1x1 Single Twist Xpressions unit		
	Skin		Size	
		SKIII	Size	
		57N 2	14.25"	w
	YW. YEAR		x	_
			14.25"	Н
	1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit	
ŀ	1 1 3	ingle (wist	Apressions unit	
	D	Skin	Size	
	19.75"		19.75"	w
	$\overline{\Gamma}$	_w →↑		
		19	Х	
		.75″ h _	19.75"	Н
	- <b>v</b>		Diamond Shown as it will appear on the	
	Diamond		Xpressions unit	
	· · · · · ·			_

It is recommended that all text and borders be 1.5" from the finish size



## Focus Area Key

focus area is always
1.5"-2.5" inside edge of all
four sides on all skin
styles and sizes

Covered by U.S. Patent No. 7,191,555.