



A	Skin	Size
		38.5" W
		x
		38.5" H
Diamond		Diamond Shown as it will appear on the Xpressions unit

B	Skin	Size
		28" W
		x
		28" H
1x1 Flat Front		1x1 Flat Front Shown as it will appear on the Xpressions unit

C	Skin	Size
		28" W
		x
		28" H
1x1 Flat Front		1x1 Flat Front Shown as it will appear on the Xpressions unit

D	Skin	Size
		28" W
		x
		28" H
1x1 Flat Front		1x1 Flat Front Shown as it will appear on the Xpressions unit

E	Skin	Size	F	Skin	Size	G	Skin	Size
		28" W			28" W			28" W
		x			x			x
		28" H			28" H			28" H
1x1 Flat Front		1x1 Flat Front Shown as it will appear on the Xpressions unit	1x1 Flat Back		1x1 Flat Front Shown as it will appear on the Xpressions unit	1x1 Flat Back		1x1 Flat Front Shown as it will appear on the Xpressions unit

H	Skin	Size	I	Skin	Size	J	Skin	Size
		28" W			28" W			38.5" W
		x			x			x
		28" H			28" H			38.5" H
1x1 Flat Back		1x1 Flat Front Shown as it will appear on the Xpressions unit	1x1 Flat Back		1x1 Flat Front Shown as it will appear on the Xpressions unit	Diamond		Diamond Shown as it will appear on the Xpressions unit

It is recommended that all text and borders be 2" from the finish size

Focus Area Key
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes
 see xpressions-snap.com for details